



T H E R M O M E T R I C S  
A C O M M I T M E N T T O E X C E L L E N C E

# NTC

## Type FP07

### Thermometrics Fastip Probe Thermistor



The NTC Type FP Series Fastip Thermoprobes consist of small diameter glass-coated thermistor beads hermetically sealed at the tips of shock resistant glass rods. The small bead thermistor has a very thin glass coating which allows for relatively flat frequency response for flow applications. As much of the bead as possible is exposed at the tip of the glass rod to provide the fastest response times. The units are rugged and unaffected by severe environmental exposures, including high density nuclear radiation.

The NTC Type FP Series Fastip Thermoprobes are ideally suited for high speed measurement and control of fluid temperatures, fluid level or flow. They offer the ease of handling associated with large glass probe thermistors as well as ultra-fast response times of small glass coated bead thermistors. These units exhibit relatively flat response to flow input from 200 Hz to 1000 Hz.

#### Features

- Ultra-Fast Response Time
- Rugged, Unaffected by Severe Environmental Exposures
- Relatively Flat Frequency Response
- Ease of Handling

#### Applications

- Sub-Sea Monitoring
- High Speed Fluid Temperature Measurement & Control
- Industrial

**Amphenol**  
**Advanced Sensors**

# Type FP07 Specifications

## Thermal and Electrical Properties

The following table lists the thermal and electrical properties for all large ruggedized thermobeads. All definitions and test methods are per MIL-PRF-23648.

Thermistor Type		FP07	
Maximum Diameter		0.085 in. (22 mm)	
Body Length		0.5 in. (12.7 mm)	
Lead Wires			
Nominal Diameter		0.012 in. (0.30 mm)	
Lead Length		0.875 in. (22 mm)	
Lead Material		Tinned dumet	
Material System			
Code Letter	R vs T Curve	25/125 Ratio	Nominal Resistance Range (Ω) @ 77°F (25°C)
E	0	5.0	-
A	1	11.8	300 to 600
A	2	12.5	680 k to 1.6 k
A	3	14.0	1.6 k to 3.6 k
A	4	16.9	3.6 k to 6.8 k
A	5	19.8	6.8 k to 27 k
A	6	22.1	-
A	7	22.7	27 k to 75 k
B	8	29.4	75 k to 130 k
B	9	30.8	130 k to 240 k
B	10	32.3	240 k to 360 k
B	11	35.7	360 k to 820 k
B	12	38.1	820 k to 13 M
B	13	45.0	1.3 M to 3.3 M
B	14	48.1	3.3 M to 6.8 M
B	15	56.5	6.8 M to 10 M
D	16	75.6	-
D	17	81.0	-

Resistance vs temperature characteristics: The nominal resistance range for the zero-power resistance at 77°F (25°C) is shown for each thermobead type and each available material system. Each material system is denoted by an ordering code letter, a referenced curve number and the nominal 77°F/257°F (25°C/125°C) resistance ratio.



NTC Type FP07 Dimensions

Thermistor Time Constant	FP07
Still Air at 77 °F (25°C)	0.10 sec
Plunge into Water	7 msec
Dissipation Constant	
Still Air at 77 °F (25°C)	0.05 mW/°C
Still Water at 77 °F (25°C)	0.25 mW/°C
Power Rating (in air)	
Maximum Power Rating	0.006 Watts

## Ordering Information

The code number to be ordered may be specified as follows:

Code	Model Number
FP	07
	Code D
	Probe Length
	0.5 (12.7 mm)
	(Other lengths available on special order)
	Code X
	Material System Code
	See Thermal and Electrical Properties table
	Code 103
	Zero Power Resistance
	See note below*
	Code
	Tolerance @ 77°F (25°C)**
	F 1
	G 2
	J 5
	K 10
	L 15
	M 20
	N 25
	P 30
	Q 40
	R 50
	S Non-standard (consult factory)
FP	___
	___
	___
	___
	___
	Typical model number

\*The zero-power resistance at 77°F (25°C), expressed in ohms (Ω), is identified by a three digit number. The first two digits represent significant figures and the last digit specifies the number of zeros to follow. Example: A Fastip probe with a 7 msec response time in water, 10 kΩ ±25% at 77°F (25°C) would be coded FP07DA103N.

\*\*Special tolerances are available on request. To specify a non-standard tolerance, use the letter 'S' followed by the desired tolerance (i.e., S7 = ±7%).

# Amphenol

## Advanced Sensors

[www.amphenol-sensors.com](http://www.amphenol-sensors.com)

© 2014 Amphenol Corporation. All Rights Reserved. Specifications are subject to change without notice. Other company names and product names used in this document are the registered trademarks or trademarks of their respective owners.

## Данный компонент на территории Российской Федерации

### Вы можете приобрести в компании MosChip.

Для оперативного оформления запроса Вам необходимо перейти по данной ссылке:

<http://moschip.ru/get-element>

Вы можете разместить у нас заказ для любого Вашего проекта, будь то серийное производство или разработка единичного прибора.

В нашем ассортименте представлены ведущие мировые производители активных и пассивных электронных компонентов.

Нашей специализацией является поставка электронной компонентной базы двойного назначения, продукции таких производителей как XILINX, Intel (ex.ALTERA), Vicor, Microchip, Texas Instruments, Analog Devices, Mini-Circuits, Amphenol, Glenair.

Сотрудничество с глобальными дистрибьюторами электронных компонентов, предоставляет возможность заказывать и получать с международных складов практически любой перечень компонентов в оптимальные для Вас сроки.

На всех этапах разработки и производства наши партнеры могут получить квалифицированную поддержку опытных инженеров.

Система менеджмента качества компании отвечает требованиям в соответствии с ГОСТ Р ИСО 9001, ГОСТ РВ 0015-002 и ЭС РД 009

### Офис по работе с юридическими лицами:

105318, г.Москва, ул.Щербаковская д.3, офис 1107, 1118, ДЦ «Щербаковский»

Телефон: +7 495 668-12-70 (многоканальный)

Факс: +7 495 668-12-70 (доб.304)

E-mail: [info@moschip.ru](mailto:info@moschip.ru)

Skype отдела продаж:

moschip.ru

moschip.ru\_4

moschip.ru\_6

moschip.ru\_9