



Drinking Cup Liner and Lid tested for safety per the U.S. Public Law 110 - 314, Consumer Product Safety, Improvement Act of 2008, Title I, Section 108 & California proposition 65.

Test Method: CPSC-CH-C1001-09.3 (Composite Test)

Di-butyl phthalate	<0.015%
Butyl-benzyl phthalate	<0.015%
Di-(2-ethyl-hexyl) phthalate	<0.015%
Di-n-octyl phthalate	<0.015%
Di-iso-nonyl phthalate	<0.015%
Di-iso-decyl phthalate	<0.015%
Di-n-hexyl phthalate	<0.015%

Independent test laboratory report available upon request.

Description

- **Replacement for static generating foam and plastic cups or water bottles on the workstation**
- **ESD Protective -**
 - Bottom covered with slip resistant conductive rubber
 - Low charging
 - Stainless steel portion grounded when picked up by a grounded operator or when placed on a grounded ESD worksurface < 1 second Charge decay $\pm 1,000$ volts to ± 100 volts tested per IEC 61340-5-1-1998 Test method B2
 - Bottom and cylindrical cup portions $R_s < 1 \times 10^9$ ohms per ANSI/ESD STM11.13
- **Thermal Insulated Drinking Cup - Perfect for hot or cold drinks. Drinking liner and inner portion of lid are insulative plastic to ensure personnel safety**
- **Reusable**
- **16 ounces (470 mL), 7.5 inches (19.5 cm) tall**
- **Double wall with Stainless Steel exterior**
- **Stainless Steel push-on lid with slide opening**
- **BPA & toxin free**
- **Made in China**

"It should be understood that any object, item, material or person could be a source of static electricity in the work environment. Removal of unnecessary nonconductors, replacing nonconductive materials with dissipative or conductive materials and grounding all conductors are the principle methods of controlling static electricity in the workplace, regardless of the activity." [ESD Handbook ESD TR20.20-2008 section 2.4 Sources of Static Electricity]

35890	Thermal Insulated Drinking Cup, Stainless Steel, 16 oz. (470 mL)
--------------	---

Specifications and procedures subject to change without notice.

Thermal Insulated Drinking Cup, Stainless Steel, 16 oz. (470 mL)

MENDA

3651 WALNUT AVE., CHINO, CA 91710
PHONE: (909) 627-2453
WEBSITE: MendaPump.com

DRAWING NUMBER
35890

DATE:
January
2019

Данный компонент на территории Российской Федерации

Вы можете приобрести в компании MosChip.

Для оперативного оформления запроса Вам необходимо перейти по данной ссылке:

<http://moschip.ru/get-element>

Вы можете разместить у нас заказ для любого Вашего проекта, будь то серийное производство или разработка единичного прибора.

В нашем ассортименте представлены ведущие мировые производители активных и пассивных электронных компонентов.

Нашей специализацией является поставка электронной компонентной базы двойного назначения, продукции таких производителей как XILINX, Intel (ex.ALTERA), Vicor, Microchip, Texas Instruments, Analog Devices, Mini-Circuits, Amphenol, Glenair.

Сотрудничество с глобальными дистрибьюторами электронных компонентов, предоставляет возможность заказывать и получать с международных складов практически любой перечень компонентов в оптимальные для Вас сроки.

На всех этапах разработки и производства наши партнеры могут получить квалифицированную поддержку опытных инженеров.

Система менеджмента качества компании отвечает требованиям в соответствии с ГОСТ Р ИСО 9001, ГОСТ РВ 0015-002 и ЭС РД 009

Офис по работе с юридическими лицами:

105318, г.Москва, ул.Щербаковская д.3, офис 1107, 1118, ДЦ «Щербаковский»

Телефон: +7 495 668-12-70 (многоканальный)

Факс: +7 495 668-12-70 (доб.304)

E-mail: info@moschip.ru

Skype отдела продаж:

moschip.ru

moschip.ru_4

moschip.ru_6

moschip.ru_9