

**Reduce risk of carpal tunnel syndrome!**

## Heyco® Lockit™ Strain Relief Pre-Assembly Equipment

Pre-Assembly Equipment for Heyco Assembly-Friendly Lockit Series Strain Reliefs:  
**RDD Lockits** – for Double D and Round Mounting Holes.

**ST Lockits** – for Rectangular Mounting Holes.

**Pre-Assemble Lockits onto cable for faster final assembly!**

**Watch this equipment in action at [www.Heyco.com](http://www.Heyco.com)**

Click on our Strain Relief Bushings Section and then the video Evolution of the Heyco Strain Relief Bushing in the upper left square.



### **A** Headlock™ for RDD and ST Lockits

Assembly head for RDD and ST Lockit Strain Reliefs. Simply place a Lockit Strain Relief into the U opening of the assembly head. Then place the cable into the bushing body and close the head to secure the Lockit™ Strain Relief permanently onto the wire. This completed sub-assembly can then be installed with fingertip pressure into the application's mounting hole—at a later time, in a different place, for lower installed cost!



### **B** FootLock™

Assembly machine for RDD and ST Lockit Strain Reliefs. This foot-pedal activated assembly machine is identical to Autolock™, except that the gravity fed track is loaded by hand instead of by a vibratory bowl.



### **C** Autolock™ Semi-Automatic

Assembly machine for RDD and ST Lockit Strain Reliefs. Suitable for high volume production runs where batched sub-assemblies are desirable. Includes vibratory feeder bowl, track and head. The operator simply inserts the cable into the assembly head slot, then presses the foot pedal to secure the Strain Relief permanently onto the wire. This completed sub-assembly can be installed with fingertip pressure into the application's mounting hole—at a later time, in a different place, for lower installed cost!

Equipment for European requirements (motor power ratings and shielding) available, consult Heyco.

### **NEW!** **D** RDD Lockit™ Guillotine - for fastest final assembly!

Optional guillotine type cutting attachment (not pictured) for the RDD Footlock™ and Autolock™ application equipment. The Lockit™ Guillotine removes the RDD hinge after attachment to the cable, thus reducing the clearance required for easy installation of the RDD/cable assembly, into the panel.

For Part No. and ordering, please consult Heyco.

**For Lockit Strain Relief Hand Pliers see page 4-16.**

## Данный компонент на территории Российской Федерации

### Вы можете приобрести в компании MosChip.

Для оперативного оформления запроса Вам необходимо перейти по данной ссылке:

<http://moschip.ru/get-element>

Вы можете разместить у нас заказ для любого Вашего проекта, будь то серийное производство или разработка единичного прибора.

В нашем ассортименте представлены ведущие мировые производители активных и пассивных электронных компонентов.

Нашей специализацией является поставка электронной компонентной базы двойного назначения, продукции таких производителей как XILINX, Intel (ex.ALTERA), Vicor, Microchip, Texas Instruments, Analog Devices, Mini-Circuits, Amphenol, Glenair.

Сотрудничество с глобальными дистрибьюторами электронных компонентов, предоставляет возможность заказывать и получать с международных складов практически любой перечень компонентов в оптимальные для Вас сроки.

На всех этапах разработки и производства наши партнеры могут получить квалифицированную поддержку опытных инженеров.

Система менеджмента качества компании отвечает требованиям в соответствии с ГОСТ Р ИСО 9001, ГОСТ РВ 0015-002 и ЭС РД 009

### Офис по работе с юридическими лицами:

105318, г.Москва, ул.Щербаковская д.3, офис 1107, 1118, ДЦ «Щербаковский»

Телефон: +7 495 668-12-70 (многоканальный)

Факс: +7 495 668-12-70 (доб.304)

E-mail: [info@moschip.ru](mailto:info@moschip.ru)

Skype отдела продаж:

moschip.ru

moschip.ru\_4

moschip.ru\_6

moschip.ru\_9