

INSTRUCTIONS:

How to change filter

- 1 Carefully lift out the filter keeping disruption to a minimum.
- 2 Insert old filter into a polythene bag or box.
- 3 Dispose the used filter into domestic waste skip or in accordance with local regulations.
- 4 Replacement is a reversal of the above.

Location and mounting

- 1 Mount unit on a stable work surface equipped with an ac power supply.
- 2 Located unit 6" to 8" (152 to 203mm) from work area.

Maintenance

- 1 Remove mains plug.
- 2 Remove filter from unit carefully.
- 3 Using a small brush clean fan and housing, being careful not to breath in the dust.
- 4 Make sure that the fan blades spin freely.

CAUTIONS

This equipment is for industrial/laboratory use.

Indoor use only.

Altitude up to 6561 FT (2000 meters).

Maximum RH of 80% up to 88°F (31°C) decreasing to 50% RH at 104°F (40°C).

Pollution degree 2 in accordance with IEC644.

Installation category II.

Temperature range 41°F (5°C) to 104°F (40°C).

The user must be aware that if the equipment is used in a manner not specified by the manufacturer, safety may be impaired.

If the supply card is damaged, or servicing is required, this work must be carried out by the manufacturer or its service agent or a similarly qualified person in order to avoid a hazard.

**FUME
ABSORBER
SA-9-115
SA-9-E-115**



134 Marbledale Road, Tuckahoe, NY 10707
TEL: 914-793-0700 FAX: 914-793-4527
E-mail: customerservice@jonard.com
Website: www.okindustries.com

P/N 15183 REV.C



ORDERING INFORMATION

FUME ABSORBER SA-9-115 SA-9-E-115

Congratulations on your purchase of our SA-9 Series Fume Absorber. This unit has been tested and inspected by O.K. Industries prior to shipment.

FEATURES:

This Fume Absorber is designed to absorb 80% of potentially harmful contaminants that are released with the smoke while soldering. Filtration is accomplished with an activated carbon-impregnated urethane foam filter.

- Bench top fume absorber.
- High air intake (CFM) to protect operators from noxious fumes.
- Molded conductive housing (SA-9-E-115 only).
- Includes 3 replacement filters.

ORDERING GUIDE:

MODEL	DESCRIPTION
SA-9-115	3 Wire 115V 50/60Hz Fume absorber
SA-9-E-115	3 wire 115V 50/60Hz ESD safe Fume absorber
SAF-1	Spare filters 3 per package

SPECIFICATIONS:

FAN MOTOR

Power Source:	115 VAC/60Hz
Qty. of Air Absorption:	105 to 126 CFM
Maximum Power:	16W

URETHANE FOAM FILTER

Qty. of Refine Activated Carbon:	12g
Qty. of Adhesion:	4g

CONTAINS:

Filter – 3pcs.
Fan (with screws) – 1 pc.

ASSEMBLY AND OPERATING INSTRUCTIONS:

1. Install the Exhaust Air Director with 4 screws as shown in Fig. 1.
2. Slide the Hood on as shown in Fig. 2.
3. Slide in the Filter as shown in Fig. 3.
4. Plug in the AC Cord.
5. Turn on the Power Switch.
6. Adjust the angle as in Fig 4.




Fig. 1.




Fig. 2.




Fig. 3.




Fig. 4.

Данный компонент на территории Российской Федерации

Вы можете приобрести в компании MosChip.

Для оперативного оформления запроса Вам необходимо перейти по данной ссылке:

<http://moschip.ru/get-element>

Вы можете разместить у нас заказ для любого Вашего проекта, будь то серийное производство или разработка единичного прибора.

В нашем ассортименте представлены ведущие мировые производители активных и пассивных электронных компонентов.

Нашей специализацией является поставка электронной компонентной базы двойного назначения, продукции таких производителей как XILINX, Intel (ex.ALTERA), Vicor, Microchip, Texas Instruments, Analog Devices, Mini-Circuits, Amphenol, Glenair.

Сотрудничество с глобальными дистрибьюторами электронных компонентов, предоставляет возможность заказывать и получать с международных складов практически любой перечень компонентов в оптимальные для Вас сроки.

На всех этапах разработки и производства наши партнеры могут получить квалифицированную поддержку опытных инженеров.

Система менеджмента качества компании отвечает требованиям в соответствии с ГОСТ Р ИСО 9001, ГОСТ РВ 0015-002 и ЭС РД 009

Офис по работе с юридическими лицами:

105318, г.Москва, ул.Щербаковская д.3, офис 1107, 1118, ДЦ «Щербаковский»

Телефон: +7 495 668-12-70 (многоканальный)

Факс: +7 495 668-12-70 (доб.304)

E-mail: info@moschip.ru

Skype отдела продаж:

moschip.ru

moschip.ru_4

moschip.ru_6

moschip.ru_9