


Jewel®



Wristband Circumference - 2.5" - 14"

Jewel® MagSnap Wrist Straps meet or exceed the requirements of ANSI/ESD S20.20 and ANSI/ESD S1.1 including section 5.4 Breakaway Force "With the ground cord connected to the cuff in a normal manner, a force of $\geq .45$ kg (1 lb) but ≤ 2.3 kg (5 lb) applied to the ground cord, in the normal disconnect direction, shall be required to separate the ground cord from the cuff."

Per ANSI/ESD S20.20 Paragraph 6.2.2.1. Personnel Grounding Requirements "All personnel shall be bonded or electrically connected to ground or contrived ground when handling ESD sensitive items. When personnel are seated at ESD protective workstations, they shall be connected to the common point ground via a wrist strap system."

"At first glance, the ground cord appears to be a relatively simple assembly. However, the design requirements are considerable, given the wide range of user applications and the durability requirements of constant tugging, flexing, and dragging over the edge of workstation tops and equipment chassis."
(ESD Handbook TR20.20 paragraph 5.3.2.2.2 Wrist Strap Ground Cord)

NOTE: Complete wrist strap kits include an alligator clip. Wrist strap kits include an alligator clip for occasions when a grounded banana jack is not available. However, "Wrist strap ground cords must be connected to a groundable point or an equipotential bonding point. Do not connect to a snap on a dissipative mat unless it is the groundable point for the mat. Do not clip a wrist strap to the edge of a dissipative mat." (ESD Handbook TR20.20 section 5.3.2.7)

ESD Handbook TR 20.20 paragraph 5.3.2.4.4 Test Frequency "Because wrist straps have a finite life, it is important to develop a test frequency that will guarantee integrity of the system. Typical test programs recommend that wrist straps that are used daily should be tested daily. However, if the products that are being produced are of such value that knowledge of a continuous, reliable ground is needed, and then continuous monitoring should be considered or even required"

Continuous Monitors pay for themselves improving quality, productivity, eliminating wrist strap daily testing and test result logging. Per ESD-S1.1 paragraph 6.1.3 Frequency of Functional Testing "Daily (Wrist Strap) testing may be omitted if constant monitoring is used."

- **Revolutionary magnetic interconnect technology**
Creates magnetic connection between wristband and coil cord; meets ANSI/ESD S20.20 and ESD S1.1, including disengagement force tests (1-5 lbs). More consistent disengagement force than standard 4 mm designs.
- **Dual-wire wrist strap provides redundancy**
If one dual wire wrist strap conductor is severed, operator still has reliable path-to-ground with other wire
- **3.5 mm mono plug compatible with 3M and other brand Continuous Monitors**
- **More reliable design**
MagSnap revolutionary design provides consistent retention and release performance.
- **Comfortable, adjustable wristband**
Made of silver suffused monofilament conductive interior
- **Woven Silveron™ fabric infused with silver monofilament conductive fiber**
Reliably removes generated static charges and is hypo-allergenic
- **Adjustable**
Only one item to stock; may be fitted to almost all people
- **Locking clasp**
Band locked so it will not slip
- **UL Listed 90P1C**

Note: This product is not recommended for use on equipment with operating voltage exceeding 250 VAC.

CAUTION: The ESD Series is for electrostatic control. It will not reduce or increase your risk of receiving electric shock when using or working on electrical equipment. Follow the same precautions you would use without wrist straps, including:

- Make certain that equipment having a grounding type plug is properly grounded.
- Make certain that you are not in contact with grounded objects other than through the ESD Series.

- **Covered by one or more of the following patents:**
Wristband: 4,577,256; 4,639,825
- **Superior warranty - See details of 1 year Limited Warranty at**
www.Desco.com/LimitedJewelWarranty.aspx
- **Made in America**

Item	Description
19823	Jewel® MagSnap Dual-Wire Adjustable Elastic Wristband
19824	Jewel® MagSnap Dual-Wire Adjustable Elastic Wrist Strap with 6 ft Coil Cord
19825	Jewel® MagSnap Dual-Wire Adjustable Elastic Wrist Strap with 12 ft Coil Cord

See Drawing [19820](#) for details on Jewel® MagSnap Dual-Wire Coil Cords

Improve wrist strap contact with Reztore™ ESD Hand Lotion.

Unless otherwise noted, tolerance is $\pm 10\%$

Specifications and procedures subject to change without notice.



Made in the
United States of America

Jewel® MagSnap Dual-Wire Adjustable Elastic Wrist Strap

DESCO WEST: 3651 WALNUT AVE., CHINO, CA 91710 WEB SITE: Desco.com
PHONE (909) 627-8178
DESCO EAST: ONE COLGATE WAY, CANTON, MA 02021-1407
PHONE (781) 821-8370

**DRAWING
NUMBER**
19823

DATE:
March
2018

DESCO

Данный компонент на территории Российской Федерации

Вы можете приобрести в компании MosChip.

Для оперативного оформления запроса Вам необходимо перейти по данной ссылке:

<http://moschip.ru/get-element>

Вы можете разместить у нас заказ для любого Вашего проекта, будь то серийное производство или разработка единичного прибора.

В нашем ассортименте представлены ведущие мировые производители активных и пассивных электронных компонентов.

Нашей специализацией является поставка электронной компонентной базы двойного назначения, продукции таких производителей как XILINX, Intel (ex.ALTERA), Vicor, Microchip, Texas Instruments, Analog Devices, Mini-Circuits, Amphenol, Glenair.

Сотрудничество с глобальными дистрибьюторами электронных компонентов, предоставляет возможность заказывать и получать с международных складов практически любой перечень компонентов в оптимальные для Вас сроки.

На всех этапах разработки и производства наши партнеры могут получить квалифицированную поддержку опытных инженеров.

Система менеджмента качества компании отвечает требованиям в соответствии с ГОСТ Р ИСО 9001, ГОСТ РВ 0015-002 и ЭС РД 009

Офис по работе с юридическими лицами:

105318, г.Москва, ул.Щербаковская д.3, офис 1107, 1118, ДЦ «Щербаковский»

Телефон: +7 495 668-12-70 (многоканальный)

Факс: +7 495 668-12-70 (доб.304)

E-mail: info@moschip.ru

Skype отдела продаж:

moschip.ru

moschip.ru_4

moschip.ru_6

moschip.ru_9