


This exploded view diagram illustrates the assembly of a mechanical device. The central component is a main housing (46) which features a front panel (67) and a base plate (20). Various sub-assemblies are shown being attached to this main unit. On the left, a bracket assembly (24, 29, 30, 33) is shown being mounted. Below it, a spring-loaded mechanism (25, 26, 27, 31, 32) is detailed. To the right, a complex assembly of components (1, 2, 3, 4, 5, 11, 12, 13, 14, 15, 16, 17, 18, 19, 21, 22, 23, 26, 27, 28, 29, 30, 31, 32, 33, 34, 35, 36, 37, 38, 39, 40, 41, 42, 43, 44, 45, 46, 47, 48, 49, 50, 51, 52, 53, 54, 55, 56, 57, 58, 59, 60, 61, 62, 63, 64, 65, 66, 67, 68, 69, 70, 71, 72, 73, 74, 75, 76, 77, 78, 79, 80, 81, 82, 83, 84, 85, 86, 87, 88, 89, 90, 91, 92, 93, 94, 95, 96, 97, 98, 99, 100) is shown, including a spring (12), a bracket (11), and a base plate (16). The diagram uses numbered circles (1-100) to identify individual parts and arrows to show the assembly sequence and orientation. Some parts are marked with 'REF' (reference) or 'C' (center). The assembly is shown in a disassembled state to clearly show the relationship between the various components.

VIEW B ROTATED 180°

POST FEED 40 mm STROKE	POST FEED 30 mm STROKE	PRE FEED 30 mm STROKE	PRE FEED 40 mm STROKE

ON INSTALLATION, SET WIRE
DISC TO LARGEST WIRE SIZE
SETTING. USE OF SETTINGS
BELOW MIN REQUIRED CRIMP
HEIGHT SETTING WILL CAUSE
DAMAGE TO CRIMP TOOLING.



GUIDE OFF
INSULATION BARREL

		C	ECR-06-006386
		B	ECR-06-004903
P	F	LTR	REVISION RECORD

	-	1	1	1	1	1	1	1528453	PRINT, APPLICATOR LOG SHEET	73
	-	1	1	1	1	1	1	1338705-3	DOCUMENTATION PACKAGE	72
										71
										70
										69
										68
	-	1	1	1	1	1	1	461264-5	PLATE, IDENTIFICATION	67
	-	2	2	2	2	2	2	21017-2	SCR,DRIVE (#2x.19) ID PLATE	66
										65
										64
	-	1	1	1	1	1	1	3-18031-0	SCR,SKT SET (M6X6) RAM	63
										62
	-	2	2	2	2	2	2	1-18024-4	SCR,BHC (M5X20) DRAG	61
	-	1	1	1	1	1	1	18024-7	SCR,BHC (M4X10) ANVIL	60
	-	1	1	1	1	1	1	5-18022-2	SCR,HEX (M4X8) FEED FINGER	59
										58
										57
	-	1	1	1	1	1	1	1338685-1	PAWL, FEED	56
	-	1	-	-	1	-	-	1338723-1	HOLDER,SHEAR, REAR (NO CUT)	55
	-	4	4	4	4	4	4	18024-8	SCR,BHC (M4x12) SHEAR HOLDER	54
	-	2	2	2	2	2	2	1-18023-3	SCR,SHC (M4x16) TERM HLD DWN	53
										52
										51
										50
	-	1	1	1	1	1	1	18024-3	SCR,BHC (M3X10) CAM	49
	-	-	1	-	-	1	-	1338675-1	CAM, PRE FEED 30 & 40 mm ST	48
	-	1	-	1	1	-	1	1338676-1	CAM, POST FEED 30 & 40 mm ST	47
	-	1	1	1	1	1	1	1320999-3	APPLICATOR BASIC SUBASSY	46
	-	1	1	1	1	1	1	690191-1	PLUG, NYLON	45
	-	1	1	1	1	1	1	1338660-1	RAM	44
										43
										42
	-	1	1	1	1	1	1	2-18024-6	SCR,BHC (M8X25) RAM	41
										40
	-	1	1	1	1	1	1	690125-1	SHIM SUBASSY	39
	-	1	1	1	1	1	1	469367-8	SPACER, FINE ADJUST	38
	-	1	1	1	1	1	1	879103-3	FINE ADJUST HEAD SUBASSY	37
										36
										35
										34
	-	2	2	2	2	2	2	1-18024-0	SCR,BHC (M4X20) STRIP GUIDE	33
	-	1	1	1	1	1	1	18027-2	WASHER, FLAT (M4)	32
	-	1	1	1	1	1	1	1-18023-2	SCR,SKT CAP (M4X12) MOUNT BLOCK	31
	-	1	1	1	1	1	1	1320908-9	SPACER, STRIP GUIDE	30
	-	1	1	1	1	1	1	1633073-1	STRIP GUIDE PLATE ASSY	29
										28
	-	2	2	2	2	2	2	1-22284-0	SPRING, DRAG	27
	-	1	1	1	1	1	1	356835-1	LEVER, DRAG RELEASE	26
	-	1	1	1	1	1	1	240792-1	DRAG, TERMINAL	25
	-	1	1	1	1	1	1	1320928-1	PLATE, STRIP GUIDE	24
	-	1	1	1	1	1	1	980371-4	SCR,SHC SHLD	23
	-	1	-	1	1	-	1	690472-2	STRIPPER	22
	-	1	1	1	1	1	1	1-18023-1	SCR,SHC (M4X10) STRIPPER	21
	-	4	4	4	4	4	4	18025-2	WASHER,LOCK (M4) STRIPPER	20
	-	-	1	-	-	1	-	690472-1	STRIPPER	19
	-	1	1	1	1	1	1	690518-1	HOLDER, TERMINAL	18
	-	1	-	-	1	-	-	1338684-1	HOLDER, SHEAR, FRONT (NO-CUT)	17
	-	2	2	2	2	2	2	18023-2	SCR,SHC (M3X6) REAR SHEAR PL	16
	-	1	1	1	1	1	1	1-690464-0	PLATE, SHEAR (REAR)	15
	-	-	1	1	-	1	1	1320920-1	HOLDER, SHEAR, REAR (CUT)	14
	-	1	1	1	1	1	1	1-690463-1	SHEAR, FLOAT (REAR)	13
	-	2	2	2	2	2	2	5-22280-0	SPRING, SHEAR	12
	-	2	2	2	2	2	2	356885-1	STOP, SHEAR	11
	-	-	1	1	-	1	1	1320921-1	HOLDER, SHEAR, FRONT (CUT)	10
	-	1	1	1	1	1	1	462006-1	SHEAR, FLOAT (FRONT)	9
1	2	2	2	1	1	1	1	1333200-7	ANVIL	8
	-	1	1	1	1	1	1	3-240641-0	SPACER, DEPRESSOR (REAR)	7
	-	1	1	1	1	1	1	690468-2	DEPRESSOR, SHEAR (REAR)	6
	-	1	1	1	1	1	1	2-455889-9	DEPRESSOR, SHEAR (FRONT)	5
	-	1	1	1	1	1	1	238011-7	SPACER, BLOCK CRIMPER	4
1	2	2	2	1	1	1	1	5-683454-4	CRIMPER, INSULATION	3
	-	1	1	1	1	1	1	455888-4	SPACER, CRIMPER	2
1	2	2	2	1	1	1	1	456400-9	CRIMPER, WIRE	1
-77	-76	-72	-71	-6	-2	-1		PART NO	DESCRIPTION	ITEM NO
← REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)										

QTY REQD PER ASSY				PARTS LIST			
		DIMENSIONS: mm [INCHES] DO NOT SCALE PRINT.		MATL		HT TR	
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		235EP04		F. BACKHURST	
		1 PLC DEC ±		DR L.OFHOUSE		AMP	
		2 PLC DEC ±		CHK -		REL 21-10-04	
		3 PLC DEC ±				M.C.LIFFORD	
		ANGLES ±		NAME		MACHINE REF	
		SURF TEXTURE: ✓		FINE ADJ SIDE FD HD-I APPL		HD-I APPL	
CE	MAROB	REMOVE BURRS, BREAK		SCALE		DWG NO	
APP	MAROB	SHARP EDGES RO.38 MAX		-		1528453	
APP	DATE	CAGE CODE		SHEET		REV	
		00779		1 of 1		C	
CUSTOMER AND ASSEMBLY DRAWING						RESTRICTED TO	
						-	

Данный компонент на территории Российской Федерации

Вы можете приобрести в компании MosChip.

Для оперативного оформления запроса Вам необходимо перейти по данной ссылке:

<http://moschip.ru/get-element>

Вы можете разместить у нас заказ для любого Вашего проекта, будь то серийное производство или разработка единичного прибора.

В нашем ассортименте представлены ведущие мировые производители активных и пассивных электронных компонентов.

Нашей специализацией является поставка электронной компонентной базы двойного назначения, продукции таких производителей как XILINX, Intel (ex.ALTERA), Vicor, Microchip, Texas Instruments, Analog Devices, Mini-Circuits, Amphenol, Glenair.

Сотрудничество с глобальными дистрибьюторами электронных компонентов, предоставляет возможность заказывать и получать с международных складов практически любой перечень компонентов в оптимальные для Вас сроки.

На всех этапах разработки и производства наши партнеры могут получить квалифицированную поддержку опытных инженеров.

Система менеджмента качества компании отвечает требованиям в соответствии с ГОСТ Р ИСО 9001, ГОСТ РВ 0015-002 и ЭС РД 009

Офис по работе с юридическими лицами:

105318, г.Москва, ул.Щербаковская д.3, офис 1107, 1118, ДЦ «Щербаковский»

Телефон: +7 495 668-12-70 (многоканальный)

Факс: +7 495 668-12-70 (доб.304)

E-mail: info@moschip.ru

Skype отдела продаж:

moschip.ru

moschip.ru_4

moschip.ru_6

moschip.ru_9