


Flow Element - EK-P4 Evaluation Kit

For SDP3x Differential Pressure Sensors



Preface

Sensirion's differential pressure sensors are commonly used for measuring the air flow in a bypass configuration. Especially for high volume and cost sensitive applications the differential pressure sensor in bypass is the ideal solution. If the flow element (also known as: flow body, main pass, orifice or pressure drop element), is produced with small dimensional tolerances, no recalibration of every single device is required. This reduces costs even more.

For more information about using Sensirion's differential pressure sensor in a bypass configuration, read the technical white paper: "Efficient Flow measurement in bypass", which can be found on our website.

1 Introduction

The EK-P4 is the evaluation kit for Sensirion's ultra-small differential pressure sensor SDP3x. The small size and low weight of the SDP3x make new applications possible. Its small size also comes with its challenges for integration and evaluation. The EK-P4 evaluation kit includes a flow element to make easy flow measurement evaluation in bypass of the SDP3x possible, and is an example on how to design the SDP3x into a target application.

The flow elements are produced for evaluation purposes only.

2 Differential Pressure to Flow Conversion

The SDP3x is calibrated for differential pressure. For flow measurements with the flow element the differential pressure (DP) needs to be converted to Standard Liters per Minute (slm). The values in the table below can be used for this conversion.

Disclaimer: These values are for information purpose only. The flow-elements are not tested and calibrated on a single device basis, and therefore no guarantee on accuracy can be given.

| DP (Pa) | Flow (slm) |
|---------|------------|---------|------------|---------|------------|---------|------------|---------|------------|
| 0.00 | 0.0 | 6.65 | 17.2 | 35.70 | 45.1 | 82.38 | 73.0 | 258.42 | 141.3 |
| 0.15 | 1.1 | 8.09 | 19.3 | 38.76 | 47.2 | 86.52 | 75.1 | 274.74 | 146.5 |
| 0.32 | 2.1 | 9.65 | 21.5 | 41.94 | 49.4 | 97.57 | 80.5 | 304.68 | 155.6 |
| 0.54 | 3.2 | 11.35 | 23.6 | 45.21 | 51.5 | 109.38 | 85.9 | 322.50 | 161.0 |
| 0.79 | 4.3 | 13.18 | 25.8 | 48.59 | 53.7 | 121.82 | 91.2 | 340.83 | 166.3 |
| 1.07 | 5.4 | 15.15 | 27.9 | 52.06 | 55.8 | 134.98 | 96.6 | 359.43 | 171.7 |
| 1.39 | 6.4 | 17.26 | 30.1 | 55.62 | 58.0 | 148.59 | 102.0 | 378.05 | 177.1 |
| 1.75 | 7.5 | 19.51 | 32.2 | 59.24 | 60.1 | 162.57 | 107.3 | 397.91 | 182.4 |
| 2.13 | 8.6 | 21.92 | 34.3 | 62.92 | 62.2 | 183.30 | 115.1 | 419.05 | 187.8 |
| 2.52 | 9.7 | 24.43 | 36.5 | 66.67 | 64.4 | 197.59 | 120.3 | 439.32 | 193.2 |
| 2.93 | 10.7 | 27.07 | 38.6 | 70.48 | 66.5 | 212.03 | 125.6 | 461.50 | 198.5 |
| 4.08 | 12.9 | 29.84 | 40.8 | 74.38 | 68.7 | 226.90 | 130.8 | 484.33 | 203.9 |
| 5.32 | 15.0 | 32.71 | 42.9 | 78.35 | 70.8 | 242.51 | 136.0 | 507.99 | 209.3 |

Typical device to device variation is estimated to be around 10% m.v (3sigma).

3 Form Factor

The flow element is designed to fit on the SDP3x evaluation kit: EK-P4. The EK-P4 includes two screws to fix the flow element to the PCB.

The 22mm medical cones provide the pneumatic connections to the flow element. The medical cones might not be within specifications and can have leaks because of small molding imperfections.

4 Flow Element Availability

The flow element has been included in the EK-P4 evaluation kit for demonstration and quick evaluation purposes, and is not for sale separately.

In case the target application needs a flow element it is important to consider the following points:

- Making a custom and reliable flow element is doable, but not necessarily cheap and easy, because of injection molding tooling.
- It is estimated that for volumes below 2000 pieces per year it is probably not economical to develop a flow element. In this case Sensirion's complete flow sensor solutions are advised, for example the SFM3000 or SFM4100.
- For yearly volumes above 2000 pieces a custom flow element could be the most cost effective solution, but the development, which is often iterative and trial and error, should not be underestimated.
- The STEP file of the flow element is available on request.

For more information on how to integrate the SDP3x in your system, consult the SDP3x Engineering Guidelines in the download center on www.sensirion.com or contact Sensirion.

Revision History

| Date | Version | Author | Changes |
|----------|---------|--------|---------------|
| Oct 2016 | V0.1 | ANB | Initial Draft |
| | | | |

Copyright© 2016, SENSIRION.
 CMOsens® is a trademark of Sensirion
 All rights reserved

SENSIRION AG
 Laubisruetistr. 50
 CH-8712 Staefa ZH
 Switzerland

phone: +41 44 306 40 00
 fax: +41 44 306 40 30
info@sensirion.com
www.sensirion.com

Sensirion Taiwan Co. Ltd.
 phone: +41 44 306 40 00
info@sensirion.com

Sensirion Inc., USA
 phone: +1 805 409 4900
info-us@sensirion.com
www.sensirion.com

Sensirion Japan Co. Ltd.
 phone: +81 3 3444 4940
info-jp@sensirion.com
www.sensirion.co.jp

To find your local representative, please visit www.sensirion.com/contact

Sensirion Korea Co. Ltd.
 phone: +82 31 337 7700~3
info-kr@sensirion.com
www.sensirion.co.kr

Sensirion China Co. Ltd.
 phone: +86 755 8252 1501
info-cn@sensirion.com
www.sensirion.com.cn

Данный компонент на территории Российской Федерации**Вы можете приобрести в компании MosChip.**

Для оперативного оформления запроса Вам необходимо перейти по данной ссылке:

<http://moschip.ru/get-element>

Вы можете разместить у нас заказ для любого Вашего проекта, будь то серийное производство или разработка единичного прибора.

В нашем ассортименте представлены ведущие мировые производители активных и пассивных электронных компонентов.

Нашей специализацией является поставка электронной компонентной базы двойного назначения, продукции таких производителей как XILINX, Intel (ex.ALTERA), Vicor, Microchip, Texas Instruments, Analog Devices, Mini-Circuits, Amphenol, Glenair.

Сотрудничество с глобальными дистрибуторами электронных компонентов, предоставляет возможность заказывать и получать с международных складов практически любой перечень компонентов в оптимальные для Вас сроки.

На всех этапах разработки и производства наши партнеры могут получить квалифицированную поддержку опытных инженеров.

Система менеджмента качества компании отвечает требованиям в соответствии с ГОСТ Р ИСО 9001, ГОСТ Р В 0015-002 и ЭС РД 009

Офис по работе с юридическими лицами:

105318, г.Москва, ул.Щербаковская д.3, офис 1107, 1118, ДЦ «Щербаковский»

Телефон: +7 495 668-12-70 (многоканальный)

Факс: +7 495 668-12-70 (доб.304)

E-mail: info@moschip.ru

Skype отдела продаж:

moschip.ru
moschip.ru_4

moschip.ru_6
moschip.ru_9