






NOTES:

- 1 INSERTION LOSS $\leq 0,1\text{dB}$, MEASURED AGAINST REFERENCE CONNECTOR AT 850nm & 1300nm
- 2 RETURN LOSS $\geq 35\text{dB}$ (FOR MTRJ 25dB), MEASURED IN MATED CONDITION AT 850nm & 1300nm
- 3 THE CASE IS DESIGNED FOR MEASUREMENTS TO BE PERFORMED ACCORDING TO ISO/IEC 14763-3
- 4 CARRY FOLDER WITH ALL DOCUMENTATION IS PACKED IN THE CASE:
 - ALL MEASUREMENT DATA SHEETS
 - CONNECTOR ENDFACE GEOMETRY DOCUMENTS
 - MANUAL 412-19083 FOR CLEANING AND CORRECT USE OF TEST LEADS AND MEASUREMENTS
- 5 MINIMUM BEND RADIUS FOR TEST: 25mm
- 6 MINIMUM BEND RADIUS FOR STORAGE: 25mm

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COOLEN 06JUN2006	tyco Electronics Tyco Electronics Nederland BV 's-Hertogenbosch, Netherlands								
		CHK F. v. GEIJN 11 SEP 06									
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD T. vd. MEULEN 11 SEP 06	NAME							
		0 PLC ± -	PRODUCT SPEC	FOCASE MM 50/125 OM2 POWER METER LAUNCH CASE							
		1 PLC ± -	—								
		2 PLC ± -	APPLICATION SPEC								
		3 PLC ± -	—								
		4 PLC ± -									
		ANGLES ± -									
MATERIAL	FINISH	WEIGHT	—	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
—	—			A2	00779	C-6695241	—				
CUSTOMER DRAWING						SCALE	NTS	SHEET	1 of 2	REV	B

12	FOMM50 FIELD CALIBRATION CORD MT-RJ	6-6695598-0						1
11	FOMM50 LAUNCH/TAIL CORD MT-RJ	X-6695598-Y	2					3--5
10	CPR LEAD 1300nm	X-6695633-Y	1					3--1
9	CPR LEAD 850nm	X-6695634-Y	1					3--1
8	MTRJ RECEPTACLE SIMPLEX	0-1278017-1						3
12	FOMM50 FIELD CALIBRATION CORD FC	6-6695598-4					2	
11	FOMM50 LAUNCH/TAIL CORD FC	X-6695598-Y	4				3--4	
10	FC CPR LEAD 1300nm	X-6695633-Y	1				3--4	
9	FC CPR LEAD 850nm	X-6695634-Y	1				3--4	
8	FC RECEPTACLE SIMPLEX	0-5501506-1					5	
12	FOMM50 FIELD CALIBRATION CORD LC	6-6695598-3				2		
11	FOMM50 LAUNCH/TAIL CORD LC	X-6695598-Y	4			3--3		
10	LC CPR LEAD 1300nm	X-6695633-Y	1			3--3		
9	LC CPR LEAD 850nm	X-6695634-Y	1			3--3		
8	LC RECEPTACLE DUPLEX	0-1374352-1				3		
12	FOMM50 FIELD CALIBRATION CORD ST	6-6695598-2			2			
11	FOMM50 LAUNCH/TAIL CORD ST	X-6695598-Y	4		3--2			
10	ST CPR LEAD 1300nm	X-6695633-Y	1		3--2			
9	ST CPR LEAD 850nm	X-6695634-Y	1		3--2			
8	ST RECEPTACLE SIMPLEX	0-0502750-2			5			
12	FOMM50 FIELD CALIBRATION CORD SC	6-6695598-1		2				
11	FOMM50 LAUNCH/TAIL CORD SC	X-6695598-Y	4	3--1				
10	SC CPR LEAD 1300nm	X-6695633-Y	1	3--1				
9	SC CPR LEAD 850nm	X-6695634-Y	1	3--1				
8	SC RECEPTACLE SIMPLEX	0-6278348-4		5				2
7	MANDRELL WRAP 50 MICRON ASSEMBLY	0-1695246-5		2	2	2	2	2
6	CLEANING STICK MTRJ	0-1391089-1						10
5	CLEANING STICK 1,25mm	0-0233069-2				10		
4	CLEANING STICK 2,5mm	0-0233069-1		10	10		10	10
3	FOAC COMPRESSED AIR SPRAY	0-1206860-1		1	1	1	1	1
2	CLEANING LENS BOOK	0-0434376-1		1	1	1	1	1
1	FOAC MOLDED CASE	—		1	1	1	1	1
ITEM	DESCRIPTION	TYCO PART NUMBER	QTY	QUANTITY				

MT-RJ CONNECTIVITY:



				1
				4--0
				3--7
				3--7
				3
		2		
		3--9		
		3--9		
		3--9		
		5		
	2			
	3--8			
	3--8			
	3--8			
	3			
2				
3--7				
3--7				
3--7				
5				2
2				
3--2				
3--2				
3--2				
5				
2	2	2	2	2
				10
		10		
10	10		10	10
1	1	1	1	1
1	1	1	1	1
1	1	1	1	1

QUANTITY				
LINK — SC/PC	LINK — ST/PC	LINK — LC/PC	LINK — FC/PC	LINK — MT-RJ
EQUIPMENT ST/PC				
0-6695241-6	0-6695241-7	0-6695241-8	0-6695241-9	1-6695241-0

				1
				4--5
				4--3
				4--3
				3
		2		
		4--4		
		4--4		
		4--4		
		5		
		2		
		4--3		
		4--3		
		4--3		
		3		2
	2			
	3--8			
	3--8			
	3--8			
	5			
2				
3--3				
3--3				
3--3				
5				
2	2	2	2	2
				10
10	10	10	10	10
10	10		10	
1	1	1	1	1
1	1	1	1	1
1	1	1	1	1

QUANTITY				
LINK — SC/PC	LINK — ST/PC	LINK — LC/PC	LINK — FC/PC	LINK — MT-RJ
EQUIPMENT LC/PC				
1-6695241-1	1-6695241-2	1-6695241-3	1-6695241-4	1-6695241-5

				1
				4--2
				4--9
				4--9
				3
			2	
			4--9	
			4--9	
			4--9	
			5	2
		2		
		4--4		
		4--4		
		4--4		
		3		
	2			
	3--9			
	3--9			
	3--9			
	5			
2				
3--4				
3--4				
3--4				
5				
2	2	2	2	2
				10
		10		
10	10		10	10
1	1	1	1	1
1	1	1	1	1
1	1	1	1	1

QUANTITY				
LINK — SC/PC	LINK — ST/PC	LINK — LC/PC	LINK — FC/PC	LINK — MT-RJ
EQUIPMENT FC/PC				
1-6695241-6	1-6695241-7	1-6695241-8	1-6695241-9	2-6695241-0

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
—

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH —

DWN
R. COOLEN
CHK
F. v. GEIJN
APVD
T. vd. MEULEN
PRODUCT SPEC
APPLICATION SPEC
WEIGHT
—
CUSTOMER DRAWING

06JUN2006
11 SEP 06
11 SEP 06
—
—
—
—
—

tyco
Electronics

Tyco Electronics Nederland BV
's-Hertogenbosch, Netherlands

NAME
FOCASE MM 50/125 OM2
POWER METER LAUNCH CASE

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=6695241

RESTRICTED TO
—

SCALE
NTS

SHEET
2 of 2

REV
B

AMP 3307-7 REV 31MAR2000

Данный компонент на территории Российской Федерации

Вы можете приобрести в компании MosChip.

Для оперативного оформления запроса Вам необходимо перейти по данной ссылке:

<http://moschip.ru/get-element>

Вы можете разместить у нас заказ для любого Вашего проекта, будь то серийное производство или разработка единичного прибора.

В нашем ассортименте представлены ведущие мировые производители активных и пассивных электронных компонентов.

Нашей специализацией является поставка электронной компонентной базы двойного назначения, продукции таких производителей как XILINX, Intel (ex.ALTERA), Vicor, Microchip, Texas Instruments, Analog Devices, Mini-Circuits, Amphenol, Glenair.

Сотрудничество с глобальными дистрибьюторами электронных компонентов, предоставляет возможность заказывать и получать с международных складов практически любой перечень компонентов в оптимальные для Вас сроки.

На всех этапах разработки и производства наши партнеры могут получить квалифицированную поддержку опытных инженеров.

Система менеджмента качества компании отвечает требованиям в соответствии с ГОСТ Р ИСО 9001, ГОСТ РВ 0015-002 и ЭС РД 009

Офис по работе с юридическими лицами:

105318, г.Москва, ул.Щербаковская д.3, офис 1107, 1118, ДЦ «Щербаковский»

Телефон: +7 495 668-12-70 (многоканальный)

Факс: +7 495 668-12-70 (доб.304)

E-mail: info@moschip.ru

Skype отдела продаж:

moschip.ru

moschip.ru_4

moschip.ru_6

moschip.ru_9