

Aptina Medical Imaging Solutions



Aptina pixels provide a spectral response which produces higher color fidelity through lower cross talk.



With the increased quantum efficiency, reduced average cross talk, and a large improvement to spatial noise Aptina Sensor performance has 22% higher peak luminance SNR and achieves the same luminance SNR with 37% less light

Aptina Pixel Size ranges from 11µm to 6.6µm allowing for extremely small size pixels in high resolution



*Conditions: 18% grey target, 670 nm IRCF, 6500K, 0.9 lens trans, 15fps, f/2.8, 100 saturation

MEDICAL IMAGING

Aptina's portfolio of CMOS medical imaging solutions combined with unparalleled customer service enable medical device manufacturers to develop advanced tools for the market's challenging growth areas, such as Point of Care (POC) devices, DNA sequencing, endoscopy, etc.

Aptina's advantages in extreme low light sensitivity, small package size, low power consumption and high speed sensing allow our OEMs to lower costs while increasing accuracy and performance.

Advances in DNA sequencing technologies during the past two decades have driven breathtaking breakthroughs in our understanding of biology and biomedicine. From human disease, to microbial ecology, to evolution, Aptina is excited to contribute powerful imaging tools to scientists and researchers bringing medical diagnostics to market.

| | | | | | | |
|-----------------------|-----------------------|---------------------|--------------------|------------------------------|------------------|--|
| Low Light Sensitivity | Low Power Consumption | High Noise Immunity | High Speed Sensing | Image Brightness and Clarity | Small Pixel Size | |
|-----------------------|-----------------------|---------------------|--------------------|------------------------------|------------------|--|

| PRODUCT | MT9M114 | MT9V115 | MT9V124 | AS0260 | MT9V024/34 | AR0140CS | AR0130 |
|---------------------------|--|--|--|--|--------------------------------------|--|--|
| Sensor/SOC | SOC | SOC | SOC | SOC | Sensor | Sensor | Sensor |
| Resolution | 1.2 MP | VGA | VGA | 2.1 MP | VGA | 1.2 MP | 1.2 MP |
| Optical Format | 1/6" | 1/13" | 1/13" | 1/6" | 1/3" | 1/4" | 1/3" |
| Frame Rate* | 1.2 MP 30 fps, VGA 75 fps | 30 fps | 30 fps | 30 fps | 8 MP (4:3) 60 fps | 1.2 MP 45 fps, 720p60 | 1.2 MP 45 fps, 720p60 |
| Pixel Size | 1.9 μm | 1.75 μm | 1.75 μm | 1.4 μm | 1.4 μm | 3.0 μm | 3.75 μm |
| Pixel Technology | – | – | – | A-Pix™ technology | A-PixHS™ technology | DR-Pix™ technology | DR-Pix™ technology |
| Shutter Type ² | ERS | ERS | ERS | ERS | GS | ERS | ERS |
| CFA | Color | Color | Color | Color | Color and Mono | Color | Color and Mono |
| CRA (Degree) | 27.7 | 24 | 24 | 28 | 11.4 | 0 | 0 |
| Dynamic Range | 70.8 dB | 58 dB | 58 dB | 65 dB | 100 dB iHDR | 96 dB 2 exposure | 83.5 dB Linear |
| Signal-to-Noise | 37 dB | 33.4 dB | 33.4 dB | 33 dB | 36 dB | 41 dB | 44 dB |
| Responsivity | 2.24 V/lux-sec | 1.65 V/lux-sec | 1.65 V/lux-sec | 0.64 V/lux-sec | 4.8 V/lux-sec | 6.5 V/lux-sec | 4.0 V/lux-sec |
| Input Clock | 6 - 54 MHz | 18 - 44 MHz | 18 - 44 MHz | 6-54 MHz | 6 - 27 MHz | 6-50 MHz | 6-50 MHz |
| Output Clock | 96 MHz | 22 MHz | N/A | 96 MHz | 336 MP/s | 74.25 MHz (parallel), 148.5 MP/s (HiSPI™) | 74.25 MHz (parallel), 148.5 MP/s (HiSPI™) |
| Interface | 1-lane MIPI, 8-bit parallel | 8-bit parallel | 12-bit LVDS | 2-lane MIPI, 12-bit parallel | 10-bit LVDS | 4-lane HiSPI, 12-bit parallel | 4-lane HiSPI, 12-bit parallel |
| Operating Temp. | –30°C to +70°C | –30°C to +70°C | –30°C to +70°C | –30°C to +70°C | –30°C to +70°C | –30°C to +85°C | –30°C to +85°C |
| Package(s) | 4.65x3.85 mm ² 55-ball CSP | 2.69x2.69 mm ² 25-ball CSP | 2.69x2.69 mm ² 25-ball CSP | 6.005 mm ² 4.158 mm ² CSP | 10x10 mm ² 48-pin CLCC | 9x9 mm ² 63-ball iBGA, 10x10 mm ² 48-pin iLCC | 9x9 mm ² 63-ball iBGA, 10x10 mm ² 48-pin iLCC |

²ERS: Rolling Shutter GS: Global Shutter GRR: Global Reset Release

| PRODUCT | AR0134 | AR0331 | AR0330 | MT9P004 | MT9P006 | MT9J003 |
|------------------|---|---|--|--|--------------------------------------|---|
| Sensor/SOC | Sensor | Sensor | Sensor | Sensor | Sensor | Sensor |
| Resolution | 1.2 MP | 3.1 MP | 3.5 MP | 5 MP | 5 MP | 10 MP |
| Optical Format | 1/3" | 1/3" | 1/3" | 1/3.2" | 1/2.5" | 1/2.3" |
| Frame Rate* | 1.2 MP 54 fps, 720p60 | 1080p60 | 1080p60 | 5 MP 15 fps, 1080p30 | 5MP 15 fps, 720p60 | 10 MP 15 fps 1080p60, |
| Pixel Size | 3.75 μm | 2.2 μm | 2.2 μm | 1.75 μm | 2.2 μm | 1.67 μm |
| Pixel Technology | DR-Pix™ technology | A-Pix™ technology | A-Pix™ technology | A-Pix™ technology | – | – |
| Shutter Type | GS | ERS, GRR | ERS, GRR | ERS, GRR | ERS, GRR | ERS, GRR |
| CFA | Color, Mono | Color | Color | Color | Color | Color, Mono |
| CRA (Degree) | 0.25 | 0 | 0, 12, 21 | 11.4, 25 | 7, 27 | 0, 13.4 |
| Dynamic Range | 64 dB | 100 dB 2 exp. ALTM | 69.5 dB | 65.4 dB | 67.74 dB | 65.2 dB |
| Signal-to-Noise | 38 dB | 39 dB | 39.6 dB | 38 dB | 38.5 dB | 34 dB |
| Responsivity | 6.1 V/lux-sec | 1.9 V/lux-sec | 2.0 V/lux-sec | 0.85 V/lux-sec | 1.8 V/lux-sec | 0.31V/lux-sec |
| Input Clock | 6-50 MHz | 6-48 MHz | 6-27 MHz | 2-64 MHz | 6-96 MHz | 6-48 MHz |
| Output Clock | 74.25 MHz (parallel), 148.5 MP/s (HiSPi™) | 74.25 MHz (parallel), 148.5 MP/s (HiSPi™) | 96 MP/s (parallel), 196 MP/s (HiSPi™) | 96 MHz | 96 MP/s | 80 MP/s |
| Interface | 12-bit parallel | 4-lane HiSPi, 12-bit parallel | 2-lane MIPI, 12- bit parallel | 2-lane MIPI, 12-bit parallel | 12-bit parallel | 4-lane HiSPi, 12-bit parallel |
| Operating Temp. | –30°C to +70°C | –30°C to +85°C | –30°C to +70°C | –30°C to +70°C | –30°C to +70°C | –30C to +70C |
| Package(s) | 10x10 mm ² 48-pin iLCC, 11.43x11.43 mm ² 48-pin PLCC | 9.5x9.5 mm ² iBGA, 10x10 mm ² 48-pin iLCC | 11.43x11.43 mm ² 48-pin CLCC, 6.3x6.6 mm ² CSP | 6.63 mm ² 6.22 mm ² CSP | 10x10 mm ² 48-pin iLCC | 10x10 mm ² 48-pin iLCC, 12x12 mm ² 48-pin PLCC |

*Frame rate is at full resolution, unless otherwise noted.

Please contact medical@aptina.com for additional product information.

GETTING STARTED WITH APTINA

1. Register on www.aplina.com.
 - a. To register, visit our site, click on the top right button that states "Register".
 - b. Submit your contact information. If you have an NDA please note this.
 - c. Shortly, an Aptina representative will grant you access to Aptina website collateral.
2. If the sensor you are interested in is not on the website:
 - a. Contact your local Aptina sales representative or distributor for information.
 - b. Our distributors and sales representatives are listed on our main webpage under the section "How to Buy".
3. To evaluate, purchase an Aptina "Demo Kit" or "Headboard".
4. Please contact medical@aptina.com for more information.

Demo Kit

Demo Kit Contents Include:

1. Aptina headboard
2. Demo camera board with USB 3.0 connector
3. USB 3.0 cable
4. Tripod stand and camera tripod



Headboard

Headboard Contents Include:

1. Aptina sensor
2. Lens mount and lens



DevSuite

DevSuite includes the tools for

1. Live image tuning
2. Real-Time register access
3. Image and video capture
4. Image analysis



About Aptina

Aptina is a global provider of intelligent imaging solutions. Aptina has created unique innovations with image sensor technologies such as Aptina Clarity+™ to deliver high-quality, rich images in challenging environments. Aptina patented imaging solutions are in leading consumer electronics devices like smartphones, tablets, laptops and digital cameras, as well as industry-specific solutions for automotive, surveillance, video conferencing, scanning, medical and gaming. Learn more at www.aplina.com.



3080 North 1st Street
San Jose, CA 95134
medical@aptina.com
www.aplina.com

©2013 Aptina Imaging Corporation. All rights reserved. Products are warranted only to meet Aptina's production data sheet specifications. Products and specifications are subject to change without notice. Aptina, the Aptina logo, A-Pix, A-PixHS, DR-Pix, Clarity+, and HISPI are trademarks of Aptina Imaging Corporation. All other trademarks are the property of their respective owners.

Данный компонент на территории Российской Федерации

Вы можете приобрести в компании MosChip.

Для оперативного оформления запроса Вам необходимо перейти по данной ссылке:

<http://moschip.ru/get-element>

Вы можете разместить у нас заказ для любого Вашего проекта, будь то серийное производство или разработка единичного прибора.

В нашем ассортименте представлены ведущие мировые производители активных и пассивных электронных компонентов.

Нашей специализацией является поставка электронной компонентной базы двойного назначения, продукции таких производителей как XILINX, Intel (ex.ALTERA), Vicor, Microchip, Texas Instruments, Analog Devices, Mini-Circuits, Amphenol, Glenair.

Сотрудничество с глобальными дистрибьюторами электронных компонентов, предоставляет возможность заказывать и получать с международных складов практически любой перечень компонентов в оптимальные для Вас сроки.

На всех этапах разработки и производства наши партнеры могут получить квалифицированную поддержку опытных инженеров.

Система менеджмента качества компании отвечает требованиям в соответствии с ГОСТ Р ИСО 9001, ГОСТ РВ 0015-002 и ЭС РД 009

Офис по работе с юридическими лицами:

105318, г.Москва, ул.Щербаковская д.3, офис 1107, 1118, ДЦ «Щербаковский»

Телефон: +7 495 668-12-70 (многоканальный)

Факс: +7 495 668-12-70 (доб.304)

E-mail: info@moschip.ru

Skype отдела продаж:

moschip.ru

moschip.ru_4

moschip.ru_6

moschip.ru_9